

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 2mm Dia. x 3.0mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock #65-567 3-4 DAYS

[Other Coating Options](#)



1



€233,00

ADD TO CART

Qty 1-5

€233,00

Qty 6+

€186,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
2.00 +0.0/-0.025

Effective Focal Length EFL (mm): 3.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 1.89
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 1.6
Centering (arcmin): 30-45
Center Thickness CT (mm): 2.00 ±0.10
Center Thickness CT 1 (mm): 1.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 1.68
Radius R₂ (mm): -1.68
Radius R₃ (mm): -7.39
Edge Thickness ET (mm): 1.60
Substrate: N-PSK53A / N-LASF9
Surface Quality: 20-10
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View