

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 2X, 300mm WD, In-Line Compact I L™ Telecentric Lens



300mm WD, 2X, In-Line Version (Left) and VIS Version (Right)

Stock **#33-115** 3-4 DAYS



1



€1.170,00

ADD TO CART

Qty 1+

€1.170,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
198.90

Horizontal Field of View, 1/2" Sensor:
3.2mm

Horizontal Field of View, 2/3" Sensor:
4.4mm

Filter Thread:
M29.0 x0.50 (Female)

Maximum Diameter (mm):

31
Weight (g): 129
Horizontal Field of View, 1/3" Sensor: 2.4mm
Numerical Aperture NA, Object Side: 0.035
Working Distance Tolerance (mm): ±2
Number of Elements (Groups): 6 (5)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.049
Typical Distortion @ 588nm (%): 0.0301
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 2X
Maximum Sensor Format: 2/3"
Working Distance (mm): 300
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/28.5
Coating: N4 MgF ₂
Depth of Field (mm): ±0.3mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 4.4 x 3.3
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View