

[See all 7 Products in Family](#)

2X Mitutoyo BD Plan Apo Objective

See More by [Mitutoyo](#)



Mitutoyo Brightfield and Darkfield (BD) Infinity Corrected Objectives

Stock **#18-402** **2 In Stock**

-

1

+

€1.290⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.290,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
378-831-13	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:

Mitutoyo	Manufacturer:
Note: #18-653 or #18-652 are required for darkfield operation.	
Physical & Mechanical Properties	
61.00	Length excluding Threads (mm):
44	Maximum Diameter (mm):
340	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
100.00	Focal Length FL (mm):
2X	Magnification:
0.055	Numerical Aperture NA:
5	Resolving Power (µm):
91.00	Depth of Field (µm):
12	Field of View, 24 Diameter Field Eyepiece (mm):
34	Working Distance (mm):
435 - 655	Wavelength Range (nm):
95	Parfocal Length (mm):
N/A	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M40 x 36 TPI	Mounting Threads:
Environmental & Durability Factors	
+5 to +40	Operating Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details


- Ideal for Brightfield and Darkfield Microscopy Applications
- Long Working Distances and High Numerical Apertures
- Plan Apochromat Design

Mitutoyo Brightfield and Darkfield (BD) Infinity Corrected Objectives offer long working distances with high numerical apertures. The high-quality plan apochromatic design allows these objectives to maintain high numerical apertures and contrast while correcting chromatic aberration in the visible wavelength region. These objectives feature M40 x 36TPI mounting threads. Mitutoyo Brightfield and Darkfield (BD) Infinity Corrected Objectives are optimized for both brightfield and darkfield illumination for applications including surface inspection and advanced life science microscopy.

Technical Information

Wavelength λ (nm)	Transmittance T (%)
400	75
450	82
500	87
550	88
600	87
650	86
700	85
750	80
800	72
850	65
900	60
950	56
1000	53
1050	51
1100	50

Stock No.	BD Plan Apo	A	B	C	D	E	F	W.D.
#18-402	2X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-403	5X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-404	7.5X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-405	10X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-406	20X	75.0	7.0	40.0	32.0	42.0	44.0	20.0
#18-407	50X	82.0	8.5	40.0	32.0	42.0	44.0	13.0
#18-408	100X	89.0	10.0	40.0	31.5	42.0	44.0	6.0
Stock No.	BD Plan Apo SL	A	B	C	D	E	F	W.D.
#18-409	20X SL	64.5	7.5	40.0	31.0	42.0	44.0	30.5
#18-410	50X SL	75.0	7.0	40.0	32.0	42.0	44.0	20.0
Stock No.	BD Plan APO HR	A	B	C	D	E	F	W.D.
#18-411	50X HR	89.9	4.8	40.0	32.0	42.0	44.0	5.2
#18-412	100X HR	93.7	4.7	40.0	32.0	42.0	44.0	1.3



Units: mm