

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

26mm Dia. x 19.5mm FL, MgF₂ Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#35-064** ☐ In Stock

☐ [Other Coating Options](#)



1



€53,00

ADD TO CART

Qty 1-10

€53,00

Qty 11+

€47,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
26.00 +/-0.3

Effective Focal Length EFL (mm):
19.50 @ 587.6nm

Numerical Aperture NA:
0.67

Back Focal Length BFL (mm): 14.60
Substrate:  Liba2000+
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 20.80
Edge Thickness ET (mm): 1.4
Center Thickness CT (mm): 9.10 ±0.20
f#: 0.75
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 26.0
Radius R₂ (mm): 42..0
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant