

TECHSPEC® 2" Dia, 12" FL UV Enhanced Alum., Spherical Mirror



Stock **#43-547** ☒ In Stock

-

1

+

€170,00

ADD TO CART

Qty 1-9
€170,00

Qty 10+
€144,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/4
Diameter (inches): 2.0
Diameter (mm): 50.80 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 12.00
Effective Focal Length EFL (mm): 304.80
Radius of Curvature (mm): 609.60
Aperture (f/#): f/6
Coating: Enhanced Aluminum (250-700nm)
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference:  0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant