

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 30mm, 60mm Radius, English Goniometer



TECHSPEC® Goniometers



Stock #66-521 3-4 DAYS

- 1 +

€417,00

ADD TO CART

Qty 1-2

€417,00

Qty 3+

€363,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: English
Stage Size (mm): 30 x 30
Travel (°): ±10
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) ¼-20, (8) 2-56
Radius R (mm): 60
Resolution (arcmin): 5
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
