

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 30.0mm Diameter x 30.0mm FL, 785nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#26-150 8 In Stock**

☐ [Other Coating Options](#)

-

1

+

€69<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €69,50 each                   |
| Qty 10-25      | €62,50 each                   |
| Qty 26-49      | €56,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties


|                      |                           |
|----------------------|---------------------------|
| 30.00 +0.0/-0.025    | Diameter (mm):            |
| <1                   | Centering (arcmin):       |
| 6.90 ±0.10           | Center Thickness CT (mm): |
| 1.5                  | Edge Thickness ET (mm):   |
| 29                   | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                                   |                                  |
|-----------------------------------|----------------------------------|
| Optical Properties                |                                  |
| 30.00 @ 587.6nm                   | Effective Focal Length EFL (mm): |
| 26.13                             | Back Focal Length BFL (mm):      |
| Laser V-Coat (785nm)              | Coating:                         |
| R <sub>abs</sub> <0.25% @ 785nm   | Coating Specification:           |
| N-SF11                            | Substrate: □                     |
| 40-20                             | Surface Quality:                 |
| 1.5λ                              | Power (P-V) @ 632.8nm:           |
| λ/4                               | Irregularity (P-V) @ 632.8nm:    |
| ±1                                | Focal Length Tolerance (%):      |
| 23.54                             | Radius R <sub>1</sub> (mm):      |
| 1                                 | f/#:                             |
| 0.50                              | Numerical Aperture NA:           |
| 785                               | Design Wavelength DWL (nm):      |
| 5 J/cm <sup>2</sup> @ 785nm, 10ns | Damage Threshold, By Design: □   |


|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

- <0.25% Reflection at 785nm
  - BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
  - [405nm](#), [532nm](#), [633nm](#), 785nm, [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered
- TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).



## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---