

TECHSPEC®

30.0mm Dia. x 75.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#32-486** 3-4 DAYS
[Other Coating Options](#)

-

1

+

€45,50

ADD TO CART

Qty 1-9
€45,50
Qty 10+
€41,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):

75.00 @ 587.6nm
Back Focal Length BFL (mm): 70.95
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.10 ± 0.10
Edge Thickness ET (mm): 3.08
Radius R₁ (mm): 38.76
Clear Aperture CA (mm): 29
f/#: 2.5
Numerical Aperture NA: 0.20
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View