

TECHSPEC® 30mm Dia. x 100mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-716** 3-4 DAYS

[Other Coating Options](#)



1



€136,00

ADD TO CART

Qty 1-5

€136,00

Qty 6+

€108,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):

100.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 94.54
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 29.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 11.05 ±0.20
Center Thickness CT 1 (mm) : 8.25 ±0.10
Center Thickness CT 2 (mm) : 2.80 ±0.10
Radius R₁ (mm) : 61.36
Radius R₂ (mm) : -44.30
Radius R₃ (mm) : -128.90
Edge Thickness ET (mm) : 8.31
Substrate: ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 3.33
Numerical Aperture NA : 0.15
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View