

TECHSPEC®

3.0mm Dia. x 3.0mm FL, NIR II Coated, Plano-Convex Lens



Stock **#67-439** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€64,50

ADD TO CART

Qty 1-9
€64,50
Qty 10+
€58,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Effective Focal Length EFL (mm):

3.00 @ 587.6nm
Back Focal Length BFL (mm): 1.88
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-SF11
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 2.00 ±0.05
Edge Thickness ET (mm): 1.46
Radius R₁ (mm): 2.35
Clear Aperture CA (mm): 2.5
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant