


[See all 64 Products in Family](#)

TECHSPEC® 30mm Dia. Linear Polarizing Film (XP42-70)



Stock #71-362 **20+ In Stock**

- 1 + €24^{.50}

ADD TO CART

Volume Pricing

Qty 1-10	€24,50 each
Qty 11-25	€20,10 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:
Polarization axis is parallel to notch on polarizer edge

Physical & Mechanical Properties

30.00 +0.0/-0.3

Diameter (mm):

Thickness (mm):
0.72 ±0.1

Construction:
Polarizing Film on PMMA

Optical Properties

Coating:
Uncoated, protective film on both sides

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate:
[Polymer Film XP42-70](#)

Transmission (%):
Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm)

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98 (nominal at 555nm)

Transmission, Single (%):
42 ±2

Transmission, Parallel (%):
36.4

Transmission, Crossed (%):
<0.004 (nominal at 555nm)

Environmental & Durability Factors

Operating Temperature (°C):
-10 to +60

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available

Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information

