

TECHSPEC[®] 3.0mm Dia. x 6.0mm FL, Uncoated, Plano-Convex Lens



Stock **#32-952** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

€53^{.50}

ADD TO CART

Volume Pricing	
Qty 1-9	€53,50 each
Qty 10-24	€48,25 each
Qty 25-49	€43,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

3.00 +0.0/-0.025	Diameter (mm):
<3	Centering (arcmin):
1.80 ±0.05	Center Thickness CT (mm):
1.41	Edge Thickness ET (mm):
2.5	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
6.00 @ 587.6nm	Effective Focal Length EFL (mm):
4.81	Back Focal Length BFL (mm):
Uncoated	Coating:
N-BK7	Substrate: □
20-10	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
3.10	Radius R ₁ (mm):
2	f/#:
0.25	Numerical Aperture NA:
350 - 2200	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Wavelength Range of 350-2200nm
- Precision Diameter and Centration Tolerances Allow for Easy OEM Integration
- Wide Variety of Diameters, Focal Lengths, and Coatings
- Anti-Reflection PCX Coating Options: [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® Uncoated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. These lenses excel in optical systems by concentrating light onto a detector or imaging plane, enhancing clarity and detail. They are also valuable for a variety of applications involving emitters, detectors, lasers, and fiber optics.

Plano-Convex lenses are ideal for a multitude of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. Their uncoated design ensures consistent performance across a broad wavelength range, making them versatile and reliable components for various optical setups.

TECHSPEC® Uncoated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

These coatings minimize surface reflections and maximize light transmission across different spectral ranges, ensuring optimal performance in various imaging and photonics applications. Whether for general use or specialized needs, TECHSPEC® PCX Lenses deliver precision and adaptability to enhance the effectiveness of optical systems.

Customers can utilize TECHSPEC® Uncoated Plano-Convex (PCX) Lenses in various ways:

- For emitters and detectors, these lenses are ideal for focusing and collimating light to enhance signal detection.
- In laser applications, they can be used to focus laser beams or to couple light efficiently into optical fibers, improving the performance of laser systems.

- For fiber optics, PCX lenses help couple light between fibers and other optical components, optimizing signal transmission and minimizing loss.
- In biotech instruments such as DNA sequencers and PCR testing platforms, these lenses focus light onto samples or detectors. Their ability to provide precise light collection and focusing enhances the accuracy and reliability of optical measurements, making them essential for high-resolution imaging and detection tasks.

By integrating TECHSPEC® Uncoated PCX Lenses into these systems, customers can achieve improved optical performance and enhanced functionality across various photonics and optical applications.


TECHSPEC Uncoated Plano-Convex (PCX) Lenses are available in a variety of diameters, focal lengths, and optical materials. Plano-convex lenses are manufactured from high quality materials such as UV Grade Fused Silica, N-BK7 Optical Glass, and a wide variety of Infrared (IR) materials. Different materials are useful for a variety of applications; review our lens material selection tech note for additional information.

Technical Information



N-BK7																													
Uncoated N-BK7 Typical Transmission <table border="1"><caption>Uncoated N-BK7 Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>93</td></tr><tr><td>800</td><td>93</td></tr><tr><td>1000</td><td>93</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	400	92	600	93	800	93	1000	93	1200	93	1400	93	1600	93	1800	92	2000	91	2200	90	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
400	92																												
600	93																												
800	93																												
1000	93																												
1200	93																												
1400	93																												
1600	93																												
1800	92																												
2000	91																												
2200	90																												
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>N-BK7 with MgF₂ Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>95</td></tr><tr><td>500</td><td>98</td></tr><tr><td>600</td><td>97</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	400	95	500	98	600	97	800	95	1000	94	1200	93	1400	93	1600	93	1800	92	2000	91	2200	90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
400	95																												
500	98																												
600	97																												
800	95																												
1000	94																												
1200	93																												
1400	93																												
1600	93																												
1800	92																												
2000	91																												
2200	90																												
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>N-BK7 with VIS-EXT Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>350</td><td>95</td></tr><tr><td>400</td><td>98</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>99</td></tr><tr><td>700</td><td>99</td></tr><tr><td>800</td><td>95</td></tr><tr><td>900</td><td>85</td></tr><tr><td>1000</td><td>75</td></tr><tr><td>1100</td><td>70</td></tr><tr><td>1200</td><td>65</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	350	95	400	98	500	99	600	99	700	99	800	95	900	85	1000	75	1100	70	1200	65	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
350	95																												
400	98																												
500	99																												
600	99																												
700	99																												
800	95																												
900	85																												
1000	75																												
1100	70																												
1200	65																												
N-BK7 with VIS-NIR Coating Typical Transmission																													

	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data



;