

TECHSPEC®

30mm Dia. x 30mm FL, NIR I Inked, Double-Convex Lens



Stock **#63-652-INK** [CONTACT US](#)
[Other Coating Options](#)

-

1

+

€66,50

ADD TO CART

Qty 1-9
€66,50
Qty 10+
€59,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):

28.12
Effective Focal Length EFL (mm): 30.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 6.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.43
Radius R₁=R₂ (mm): 45.61
Clear Aperture CA (mm): 29.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View