


34mm² DUV Photodiode with Ceramic Housing



DUVPhotodiodes

Stock **#84-985** **2 In Stock**

-

1

+

€128⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€128,00 each
Qty 5-9	€114,00 each
Qty 10-24	€101,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
1 @0 V, 1 kΩ	Rise Time (µs):
Physical & Mechanical Properties	
5.8 x5.8	Size of Active Area (mm):
	Active Area (mm²):

34.0	
Optical Properties	
980.00	Peak Response Wavelength (nm):
Electrical	
0.5	Responsivity @ 980nm (AW):
Minimum: 0.1 Typical: 0.4	Shunt Resistance @ V=-10mV (GΩ):
0.34	Responsivity @ 633nm (AW):
0.12	Responsivity @ 200nm (AW):
380.00	Capacitance @ V _R =0V (pF):
5.8 x 10 ⁻¹⁴	Noise Equivalent Power NEP (W/ Hz ^{1/2}): @ 0 V, 200nm
5.00	Maximum Reverse Voltage (V):
Hardware & Interface Connectivity	
Ceramic	Connector:
Environmental & Durability Factors	
-20 to +60	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.