

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



High Performance Laser Line Bandpass Filters

Stock #64-240 3-4 DAYS

[Additional Bandwidths](#)



1



€357,00

ADD TO CART

Qty 1+

€357,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
12.50 +0.0/-0.1

Angle of Incidence (°):  
0 ±2

Bandwidth (nm):  
1.3

Beam Deviation (arcsec):  
<11

|                                                                                                       |
|-------------------------------------------------------------------------------------------------------|
| <b>OD 5 Blocking Wavelength Range (nm) :</b><br>315 - 352 & 359 - 423                                 |
| <b>OD 6 Blocking Wavelength Range (nm):</b><br>327 - 350 & 360 - 390                                  |
| <b>Optical Density OD (Average):</b><br>≥6.0                                                          |
| <b>Clear Aperture CA (mm):</b><br>≥10                                                                 |
| <b>Center Wavelength CWL (nm):</b><br>355.00                                                          |
| <b>Design Wavelength DWL (nm):</b><br>355                                                             |
| <b>Full Width-Half Max FWHM (nm):</b><br>1.35 - 2.49                                                  |
| <b>Substrate:</b> <input type="checkbox"/><br>Low Fluorescence <a href="#">N-BK7</a> or equivalent    |
| <b>Minimum Transmission (%):</b><br>>90                                                               |
| <b>Coating:</b><br>Hard Coated                                                                        |
| <b>Surface Quality:</b><br>60-40                                                                      |
| <b>Thickness Tolerance (mm):</b><br>±0.10                                                             |
| <b>Transmission (%):</b><br>>90                                                                       |
| <b>Type:</b><br>Bandpass Filter                                                                       |
| <b>Blocking Wavelength Range (nm):</b><br>315 - 352 & 359 - 423                                       |
| <b>Construction:</b><br>Mounted in Black Anodized Ring                                                |
| <b>Transmitted Wavefront, P-V:</b><br>¼ @ 633nm                                                       |
| <b>Temperature Dependence (ppm/°C):</b><br><5                                                         |
| <b>Environmental Durability:</b><br>ML-STD-810F Paragraphs 501.4, 502.4, and 507.4                    |
| <b>Physical Durability:</b><br>ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3 |
| <b>Mount Thickness (mm):</b><br>3.5 ±0.1                                                              |
| <b>Substrate Thickness (mm):</b><br>2.0 ±0.1                                                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |