

35mm 2 MegaPixel Fixed Focal Length Lens



35mm Fixed Focal Length, #14-400

Stock **#14-400** **2 In Stock**

-

1

+

€406⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€406,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
36.91	Length (mm):
Maximum Diameter (mm):	

32.5	
	Weight (g):
90	
Optical Properties	
	Horizontal Field of View @ Max Sensor Format:
14.4°	
	Horizontal Field of View, 2/3" Sensor:
14.4°	
	Horizontal Field of View, 1/2" Sensor:
10.5°	
	Horizontal Field of View, 1/3" Sensor:
8°	
	Horizontal Field of View, 1/4" Sensor:
5.23°	
	Maximum Image Circle (mm):
11.00	
	Focal Length FL (mm):
35.00	
	Working Distance (mm):
500 - ∞	
	Aperture (f/#):
f/1.4 - f/32	
	Distortion (%):
<-1	
	Lens Wavelength Range:
VIS	

Sensor	
	Maximum Sensor Format:
2/3"	

Threading & Mounting	
	Filter Thread:
M30.5 x 0.50 (Female)	
	Mount:
C-Mount	

Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover ½" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.