

[See all 21 Products in Family](#)

## 4-10mm FL C-Mount, Manual Iris, IR Corrected Lens



Image represents #22-799: Design will vary by stock number.

Stock **#22-802** **7 In Stock**

⊖ 1 ⊕ €684.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€684,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

Varifocal Lens **Type:**

### Physical & Mechanical Properties

Variable **Iris Option:**

46.50 **Length (mm):**

---

59.0 **Maximum Diameter (mm):**

67 **Weight (g):**

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
112° - 44°

4-10 **Focal Length Range (mm):**

500 - ∞ **Working Distance (mm):**

f/1.4 - Closed **Aperture (f/#):**

VS **Lens Wavelength Range:**

## Sensor

1/1.7" **Maximum Sensor Format:**

## Threading & Mounting

C-Mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.