

3mm FL, f/4, Low Distortion M12 Lens



3mm FL, Low Distortion M12 Lens

Stock **#75-200** NEW **1 In Stock**

-

1

+

€241⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€241,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:	
Ultra Low Distortion Wide Angle Lenses	
Imaging Lens Type:	
M12 Imaging Lens	

Physical & Mechanical Properties

Iris Option:	
Fixed	
Length (mm):	

22.28	
	Maximum Diameter (mm):
16.0	
	Outer Diameter (mm):
16.0	
	Weight (g):
6	
	Maximum Length (mm):
22.28	

Optical Properties	
Horizontal Field of View @ Max Sensor Format: 76.9°	
Field of View at Max Sensor Format: Horizontal: 76.9° Vertical: 61.6° Diagonal: 89.6°	
	Maximum Image Circle (mm):
7.20	
	Focal Length FL (mm):
3.00	
	Working Distance (mm):
100 - ∞	
	Aperture (f/#):
f/4	
	Maximum Distortion (%):
-0.02	
	Exit Pupil Position (mm):
-53.1	
	Lens Wavelength Range:
VIS	

Sensor	
	Optimized Sensor Format:
1/2.5"	
	Maximum Sensor Format:
1/2.5"	

Threading & Mounting	
	Mount:
S-Mbunt (M12 x0.5)	

Environmental & Durability Factors	
	Storage Temperature (°C):
-20 to +60	


Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details


- Distortion as low as -0.02%
- Up to 1/1.8", S-Mbunt Options
- 1.7mm - 5mm Focal Lengths

Ultra Low Distortion Wide Angle Lenses are designed to achieve less than -0.02% distortion over a 76.9° field of view, less than -0.32% distortion over a 109.1° field of view, or less than -0.51% distortion over a 59.8° field of view. The ultra-low distortion values of these lenses ensure imaging with straight lines and natural object shapes, helping to reduce post-processing requirements. These lenses offer high transmission from the VIS to NIR and are available in focal lengths of 1.70, 3.00, and 5.00mm. Ultra Low Distortion Wide Angle Lenses' low focal lengths allow for capturing more of the scene in a single frame. These lenses are ideal for surveillance, security, robotics, drive assistance systems, and [factory automation applications](#).


Technical Information




3mm FL, f/4, Low Distortion M12 Lens, Distortion Plot



3mm FL, f/4, Low Distortion M12 Lens, MTF Plot



3mm FL, f/4, Low Distortion M12 Lens, Relative Illumination Plot



3mm FL, f/4, Low Distortion M12 Lens, Transmission Plot