

**TECHSPEC® 3mm FL f/8.0, IR-Cut Blue Series M12 Lens**



3mm FL Blue Series M12 Lens



Stock **#20-058** 3-4 DAYS



1



€100,00

ADD TO CART

Qty 1-49

€100,00

Qty 50+

€79,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):  
16.10

Maximum Diameter (mm):  
14

|                                                                                                      |
|------------------------------------------------------------------------------------------------------|
| <b>Horizontal Field of View, 1/3" Sensor:</b><br>91.2°                                               |
| <b>Maximum Image Circle (mm):</b><br>6.00                                                            |
| <b>Numerical Aperture NA, Object Side:</b><br>0.002                                                  |
| <b>Number of Elements (Groups):</b><br>6(5)                                                          |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                           |
| <b>Type:</b><br>M12 Imaging Lens                                                                     |
| <b>Focal Length FL (mm):</b><br>3.00                                                                 |
| <b>Primary Magnification PMAG:</b><br>0.029X                                                         |
| <b>Maximum Sensor Format:</b><br>1/3"                                                                |
| <b>Working Distance (mm):</b><br>100 - ∞                                                             |
| <b>Mount:</b><br>M12 x0.5 (S-Mbunt)                                                                  |
| <b>Aperture (f/#):</b><br>f/8                                                                        |
| <b>Distortion (%):</b><br>34.76 @ Full Field                                                         |
| <b>Back Focal Length BFL (mm):</b><br>4.8 - 4.7                                                      |
| <b>Coating Specification:</b><br>λ/4 MgF <sub>2</sub> @ 550nm                                        |
| <b>Entrance Pupil Position (mm):</b><br>4.90                                                         |
| <b>Object Space Principal Plane (mm):</b><br>-6.55                                                   |
| <b>Image Space Principal Plane (mm):</b><br>2.46                                                     |
| <b>Field of View at Max Sensor Format:</b><br>Horizontal: 91.2°<br>Vertical: 68.5°<br>Diagonal: 113° |
| <b>IR Cut Filter:</b><br>Yes                                                                         |
| <b>Exit Pupil Position (mm):</b><br>-3.23                                                            |
| <b>Lens Wavelength Range:</b><br>VS (IR-Cut Filter)                                                  |
| <b>Imaging Lens Type:</b><br>High Performance M12 Lens with IR Cut Filter                            |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |