

[See all 4 Products in Family](#)

3mW 850nm, Laboratory Laser Diode



Stock **#53-760** **2 In Stock**

-

1

+

€373⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€373,00 each
Qty 10+	€355,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Note: Includes: Users Manual, Power Supply, Warning Label, and Focus Key	
Diode	Type of Laser:
IIIb	Laser Class - CDRH:

Optical Properties	
850.00	Wavelength (nm):
±5	Wavelength Tolerance (nm):
25	Beam Size at Nearest Focus (µm):
4 x2	Beam Diameter (mm):
<0.5	Beam Divergence (mrad):
Infrared	Color:
35mm - ∞	Focus Range (mm):

Electrical

3 (±5%)	Output Power (mW):
---------	--------------------

Hardware & Interface Connectivity

110/240 V AC (included)	Power Supply:
3.5 - 5 VDC, 60 mA	Power Requirement:
Free Space	Output Type:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Visible and Near IR Models
- Focusable from 20mm to Infinity

Designed as a compact diode for laboratory and industrial applications, this laser uses sophisticated electronics to promote long life and reliable performance. Its features include output power stabilization, integral drive circuitry, user adjustable collimating optics, emission indicator, beam attenuator (shutter), and electrical on/off switch (not available on IR unit). Due to its superior durability and size, it is an ideal replacement for Helium-Neon lasers or NIR sources in many applications. Typical applications include: pilot beam for alignment, measurement, robotic control and positioning. Additional features on the non-emitting end of IR unit for CDRH compliance are: key control (removal deactivates laser), remote interlock connector, safety interlocks, and delay time of 5 seconds between laser activation and actual laser output.