

[See all 21 Products in Family](#)

## 4-10mm FL, CS-Mount, P-iris, 4K Ultra Motorized with Limit Switch



Image represents #22-806: Design will vary by stock number.

Stock **#22-808** **1 In Stock**

⊖ 1 ⊕ €473<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€473,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

**Note:**  
User with Motorized Lens Control Board (#22-832)

**Type:**  
Varifocal Lens

### Physical & Mechanical Properties

**Iris Option:**  
P-iris

51.50	<b>Length (mm):</b>
59.0	<b>Maximum Diameter (mm):</b>
77	<b>Weight (g):</b>

## Optical Properties

112° - 44°	<b>Horizontal Field of View @ Max Sensor Format:</b>
4-10	<b>Focal Length Range (mm):</b>
500 - ∞	<b>Working Distance (mm):</b>
f/1.4 - Closed	<b>Aperture (f/#):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/1.7"	<b>Maximum Sensor Format:</b>
--------	-------------------------------

## Threading & Mounting

CS-Mount	<b>Mount:</b>
----------	---------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.