


[See all 11 Products in Family](#)

400µm 0.22 NA VIS/NIR Fiber, 25m Length



Stock **#57-093** **1 In Stock**

- 1 + €575⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€575,00 each
Qty 5-24	€510,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:

Fiber ends are not polished.

Physical & Mechanical Properties

440 ±8.8 Cladding Diameter (µm):

Minimum Bend Radius (mm):	
88/44 (Continuous/Momentary)	
Length (m):	
25.00	
Outer Diameter (µm):	
480 ±5	
Core Diameter (µm):	
400 ±8	
Optical Properties	
Acceptance Angle (°):	
25.4	
Coating:	
VIS/NIR	
Substrate: <input type="checkbox"/>	
Fused Silica	
Numerical Aperture NA:	
0.22	
Index of Refraction (n₁) - Core:	
1.457	
Index of Refraction (n₁) - Cladding:	
1.440	
Wavelength Range (nm):	
300 - 2400	
Numerical Aperture (NA) Tolerance:	
±0.02	
Material Properties	
Buffer Material:	
Polyimide	
Environmental & Durability Factors	
Operating Temperature (°C):	
-190 to +390	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 209:	
Compliant	
Certificate of Conformance:	
View	

Product Details

UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50µm – 600µm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600µm.

Note: Fiber ends are not polished.

Technical Information

