

400µm 0.22 NA VIS/NIR Fiber, 10m Length



Stock #57-087 3-4 DAYS

-

1

+

€226,00

ADD TO CART

Qty 1-4
€226,00
Qty 5+
€200,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Acceptance Angle (°): 25.4
Buffer Material: Polyimide
Cladding Diameter (µm):

440 ±8.8
Coating: VIS/NIR
Minimum Bend Radius (mm): 88/44 (Continuous/Momentary)
Substrate:  Fused Silica (Corning 7980)
Length (m): 10.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 480 ±5
Core Diameter (µm): 400 ±8
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.440
Wavelength Range (nm): 300 - 2400
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View