


LightPath 357786 | 2mm Dia., 0.50 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#37-108** 3-4 DAYS

- 1 + **€88,00**

ADD TO CART

Qty 1-10
€88,00
Qty 11+
€77,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
2.00 ±0.015

Effective Focal Length EFL (mm):
1.41 @488nm

Numerical Aperture NA: 0.50
Substrate:  D-Lak6
Aspheric Design Wavelength (nm): 488
Coating: BBAR (350-600nm)
Coating Specification: R _{abs} <1.0% @ 350 - 600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 1.52
Edge Thickness ET (mm): 0.19
Center Thickness CT (mm): 0.50 ±0.05
f/#: 0.71
Bevel: Protective bevel as needed
Lightpath Lens Code: 357786
Type: Aspheric Lens
Wavelength Range (nm): 350 - 600
Working Distance (mm): 1.2
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant