

TECHSPEC®

40mm Dia., 0.80 Numerical Aperture, Uncoated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-435-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + €669^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€669,00 each
Qty 6-10	€602,00 each
Qty 11-25	€549,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Aspheric Lens

Type:

Physical & Mechanical Properties

40.00 ±0.025 Diameter (mm):

<3 Centering (arcmin):

36.00 Clear Aperture CA (mm):

2.40 Edge Thickness ET (mm):

13.10 ±0.10 Center Thickness CT (mm):

Protective as needed Bevel:

Plano Shape of Back Surface:

Optical Properties

25.00 @ 587.6nm Effective Focal Length EFL (mm):

0.80 Numerical Aperture NA:

17.74 Back Focal Length BFL (mm):

[N-SF6](#) Substrate:

0.4λ Asphere Figure Error, RMS @ 632.8nm:

Uncoated Coating:

40-20 Surface Quality:

0.63 f#:

390 - 2500 Wavelength Range (nm):

Infinite Conjugate Distance:

Regulatory Compliance

[View](#) Certificate of Conformance:

PRODUCT DETAILS

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

COMPATIBLE MOUNTS