

[All Products](#) / [Optics](#) / [Windows](#) / [Sapphire Windows](#)

[See all 389 Products in Family](#)


TECHSPEC®

40mm Dia., 1mm Thick Sapphire Window

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Stock #25-433 **4 In Stock**

1

€311^{.00}

ADD TO CART

Volume Pricing	
Qty 1-24	€311,00 each
Qty 25-50	€238,00 each
Qty 51-99	€233,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):	36.00	Diameter (mm):	40.00 ±0.05
Thickness (mm):	1.00 ±0.05	Parallelism (arcmin):	≤3.5
Bevel:	Protective as needed	Clear Aperture (%):	≥90
Edges:	Fine Ground	Poisson's Ratio:	0.27
Young's Modulus (GPa):	435	Knoop Hardness (kg/mm²):	1,900.00

Optical Properties

Coating:	BBAR (1650-3000nm)	Substrate:	Sapphire (Al ₂ O ₃)
Index of Refraction (n_d):	1.77	Surface Quality:	80-50
Abbe Number (v_d):	72.24	Birefringence (n_o-n_e):	0.008 for Visible Light Orthogonal to Optical Axis
Axis Orientation:	Random	Coating Specification:	R _{avg} <1% @ 1650 - 3000nm

Wavelength Range (nm): 1650 - 3000		Surface Flatness (P-λ): 2λ (typical)	
Density (g/cm³): 3.97		(10⁻⁶ / °C): (Perpendicular to C-Axis)	
Regulatory Compliance			
RoHS 2015: Compliant		Certificate of Conformance: View	
Reach 235: Compliant			

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Features Extreme Surface Hardness Chemical Resistance
- Transmits Wavelengths Ranging From UV to Mid-Infrared
- Thinner and Stronger than Standard Glass Windows
- Anti-Reflection Coating Options Covering 350 - 5000nm Available

TECHSPEC® Sapphire Windows are manufactured from single crystal sapphire, making them ideal for demanding applications (such as laser systems) because of their extreme surface hardness, high thermal conductivity, high dielectric constant and resistance to common chemical acids and alkalis. Sapphire is the second hardest crystal next to **diamond** and, because of their structural strength, sapphire windows can be made much thinner than other common windows with improved transmittance. Chemically, sapphire is single crystal aluminum oxide (Al₂O₃) and is useful in a transmission range from UV to mid-infrared or 330 - 5500nm when uncoated. TECHSPEC® Sapphire Windows are available with anti-reflection (AR) coatings to improve performance in the visible, NIR, and IR spectra with coating options covering 350 - 5000nm.

Technical Information

Related Products



Cage System Optical Lens Mounts



C, S, and T-Mount Circular Optic Mounts



PUROSOL™ Optical Cleaner

Compatible Mounts

	Title				Buy
	40.0mm Optic Dia., Optic Mount				10 In Stock <input type="text" value="1"/>
	7.0 - 40.0mm Optic Height, English Bar-Type Optic Holder	Fixed	#03-676	€106,00 Request Quote	20+ In Stock <input type="text" value="1"/>
	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed	#55-530	€108,00 Request Quote	CONTACT US <input type="text" value="1"/>
	7.0 - 67.0mm Optic Height, English Bar-Type Optic Holder	Fixed	#03-669	€116,00 Request Quote	20+ In Stock <input type="text" value="1"/>
	8.0 - 118.0mm Optic Height, English Bar-Type Optic Holder	Fixed	#03-666	€120,00 Request Quote	20+ In Stock <input type="text" value="1"/>
	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed	#16-078	€410,00 Request Quote	CONTACT US <input type="text" value="1"/>

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Video
- Glossary
- FAQ

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

TECHNICAL TOOL

Beam Displacement Calculator

APPLICATION NOTE

Understanding Optical Windows

VIDEO

Optical Windows Review

APPLICATION NOTE

Optical Glass

[View More](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: