

TECHSPEC® 40mm Dia. x 100mm FL, VIS 0° Coated, Achromatic Lens



Stock **#63-713** 3-4 DAYS

[Other Coating Options](#)



1



€168,00

ADD TO CART

Qty 1-5

€168,00

Qty 6+

€134,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

100.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 91.24
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 13.00 ±0.20
Center Thickness CT 1 (mm): 10.00 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R ₁ (mm): 46.73
Radius R ₂ (mm): -50.61
Radius R ₃ (mm): -341.70
Edge Thickness ET (mm): 7.92
Substrate: N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View