

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 40mm Dia. X 80mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-380-INK [CONTACT US](#)

[Other Coating Options](#)



1



€190,00

ADD TO CART

Qty 1-5
€190,00

Qty 6+
€152,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

80.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 70.75
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 16.07 ±0.20
Center Thickness CT 1 (mm): 12.07 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 53.76
Radius R₂ (mm): -36.73
Radius R₃ (mm): -435.85
Edge Thickness ET (mm): 11.75
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View