


**TECHSPEC® 40mm Dia x -100mm FL Negative Doublet Lens MgF<sub>2</sub> Coated**



Stock #63-765 **20+ In Stock**

⊖ 1 ⊕ €200<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€200,00 each
Qty 6-25	€160,00 each
Qty 26-49	€150,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Negative Achromatic Lens **Type:**

**Physical & Mechanical Properties**

40.00 +0.0/-0.025 **Diameter (mm):**

39.00 **Clear Aperture CA (mm):**

<1	Centering (arcmin):
10.50 ±0.20	Center Thickness CT (mm):
4.00 ±0.10	Center Thickness CT 1 (mm):
6.50 ±0.10	Center Thickness CT 2 (mm):
15.08	Edge Thickness ET (mm):
Protective as needed	Bevel:

## Optical Properties

-100.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
-104.33	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
-60.11	Radius R <sub>1</sub> (mm):
48.43	Radius R <sub>2</sub> (mm):
149.50	Radius R <sub>3</sub> (mm):
<a href="#">N-BK7 / N-SF5</a>	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
2.5	f/#:
0.20	Numerical Aperture NA:
MgF <sub>2</sub> (400-700nm)	Coating:
R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 700	Wavelength Range (nm):

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 219:
<a href="#">View</a>	Certificate of Conformance:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Magnesium Fluoride (MgF<sub>2</sub>) Coating
- Used to Extend Focal Length
- [Broadband AR Coated Negative Achromatic Lenses](#) Also Available

TECHSPEC® MgF<sub>2</sub> Coated Negative Achromatic Lenses consist of two optical elements cemented together. Negative doublet lenses are corrected for color and on-axis aberrations. TECHSPEC MgF<sub>2</sub> Coated Negative Achromatic

## Technical Information



## Coating Curves

## Compatible Mounts