

TECHSPEC<sup>®</sup> 40mm Length, C-Mount Extension Tube



Stock #54-631 20+ In Stock

-

1

+

€52<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | €52,50 each                   |
| Qty 5-9        | €46,60 each                   |
| Qty 10-25      | €43,10 each                   |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Extension Tube

Type:

Extension Tube (Fixed)

Function:

Physical & Mechanical Properties

40.0

Extension Length (mm):

|      |                         |
|------|-------------------------|
| 44.0 | Total Length (mm):      |
| 30.0 | Outer Diameter (mm):    |
| 22.0 | Clear Aperture CA (mm): |

Threading & Mounting

|         |              |
|---------|--------------|
| C-Mount | Thread Type: |
|---------|--------------|

Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | REACH 241:                  |

## Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

## Technical Information

