

[See all 76 Products in Family](#)

TECHSPEC®

4.5mm, f/2 Ci Series Fixed Focal Length Lens



4.5mm Focal Length

Stock **#87-551** 20+ In Stock

-

1

+

€355⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-24	€355,00 each
Qty 25+	€320,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Ci Series

Series:

Fixed Focal Length Lens

Type:

Imaging Lens Type:

Compact Lens with Fixed Aperture

Physical & Mechanical Properties

Fixed	Iris Option:
32.14	Length (mm):
40	Maximum Diameter (mm):
40	Outer Diameter (mm):
66	Weight (g):
3.4	Maximum Rear Protrusion (mm):
26.50	Diameter (mm):

Optical Properties

Horizontal Field of View @ Max Sensor Format: 72.0mm - 84.7°	
Field of View at Max Sensor Format: Horizontal: 72mm - 84.8° Vertical: 50.5mm - 66.1° Diagonal: 98.2mm - 100.1°	
Horizontal Field of View, 1/1.8" Sensor: 72.0mm - 84.7°	
Horizontal Field of View, 1/2" Sensor: 53.9mm - 69.4°	
Horizontal Field of View, 1/3" Sensor: 44.0mm - 59.2°	
Horizontal Field of View, 1/4" Sensor: 32.0mm - 45.2°	
9.00	Maximum Image Circle (mm):
0.0285	Numerical Aperture NA, Object Side:
Number of Elements (Groups): 7 (6)	
4.50	Focal Length FL (mm):
Working Distance (mm): 25 - ∞	
Aperture (f/#): f/2	
Coating: 425 - 675nm BBAR	
Coating Specification: 425 - 675nm BBAR	
Entrance Pupil Position (mm): 14.4	
Object Space Principal Plane (mm): 17.89	
Image Space Principal Plane (mm): 6.51	
Maximum Distortion (%): -15.83	
Exit Pupil Position (mm): -9	
Lens Wavelength Range: VIS	

Sensor

1/1.8"	Maximum Sensor Format:
2.74	Pixel Size (μm):

Threading & Mounting

M58 x0.75 (Male)	Filter Thread:
#87-425 (Required)	Filter Thread Adapter:
M40.0 x0.5 (Male)	Front Thread:
C-Mount	Mount:

Environmental & Durability Factors

	Storage Temperature (°C):
-20 to +60	
	Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)	

Regulatory Compliance

	Certificate of Conformance:
View	

Product Details


- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- Ruggedized (Cr) Designs Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- C Series: Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a VIS-NIR Broadband Anti-Reflection (BBAR) Coating.
- Ci Series: Simplified mechanics featuring fixed apertures with compact housing. Industrial Ruggedization for reduced size, cost, and locked focus.
- Cr Series: All optics glued in place and a locking C-clamp focus ring. Stabilized Ruggedization for reduced pixel shift and improved focus stability.
- Cx Series: Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- Liquid Lens Cx Series: Designed with an integrated liquid lens for quick autofocus.
- Cw Series: Waterproof, designed to meet IEC Ingress Protection Code IPX7 and IPX9K.


Technical Information




#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Distortion Plot




#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Relative Illumination Plot




#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f2



#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f2



#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2



#87-551, 4.5mm, f/2 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm

Compatible Cameras

;