

[See all 39 Products in Family](#)

## 488nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock #64-250 [CONTACT US](#)

[Additional Bandwidths](#)

⊖ 1 ⊕ €852.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€852,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Bandpass Filter **Type:**

### Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**

≥22 **Clear Aperture CA (mm):**

**Construction:**

Mounted in Black Anodized Ring

**Physical Durability:**

ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3

**Substrate Thickness (mm):**

2.0 ±0.1

**Optical Properties****Angle of Incidence (°):**

0 ±2

**Bandwidth (nm):**

1.9

**Beam Deviation (arcsec):**

&lt;11

**OD 5 Blocking Wavelength Range (nm) :**

415 - 483 &amp; 493 - 625

**OD 6 Blocking Wavelength Range (nm):**

449 - 481 &amp; 495 - 537

**Optical Density OD (Average):**

≥6.0

**Center Wavelength CWL (nm):**

488.00

**Design Wavelength DWL (nm):**

488

**Full Width-Half Max FWHM (nm):**

1.85 - 3.42

**Substrate:** 

Fused Silica

**Minimum Transmission (%):**

&gt;90

**Coating:**

Hard Coated

**Surface Quality:**

60-40

**Transmission (%):**

&gt;90

**Blocking Wavelength Range (nm):**

415 - 483 &amp; 493 - 625

**Transmitted Wavefront, P-V:**

¼ @ 633nm

**Threading & Mounting****Mount Thickness (mm):**

3.5 ±0.1

**Environmental & Durability Factors****Temperature Dependence (ppm/°C):**

&lt;5

**Environmental Durability:**

ML-STD-810F Paragraphs 501.4, 502.4, and 507.4

**Regulatory Compliance****RoHS 2015:**[Compliant](#)**Reach 209:**[Compliant](#)**Certificate of Conformance:**[View](#)**Product Details**

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm<sup>2</sup> @ 532nm, 10ns.

**Technical Information**



## Compatible Mounts