

TECHSPEC® 464, 542 & 639nm, 50mm Dia., Tri-Band Filter



Multi-Band Fluorescence Bandpass Filters

Stock **#87-254** 3-4 DAYS

- 1 + **€1.092,00**

ADD TO CART

Qty 1-9
€1.092,00
Qty 10+
€908,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.1

Angle of Incidence (°):
0

Bandwidth (nm):
23 @ 464nm

27 @ 542nm 42 @ 639nm
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 45.34
Substrate: Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Compatible Fluorophore: CFP/YFP/Texas Red Emission
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25
Multi-Band Center Wavelengths (nm): 464, 542, 639

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant