

[See all 130 Products in Family](#)

TECHSPEC<sup>®</sup> 4mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC<sup>®</sup> Nd:YAG Laser Line Mirrors



Stock #12-623 14 In Stock

-

1

+

€118<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €118,00 each                  |
| Qty 6-25       | €105,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

|                                             |                                                       |
|---------------------------------------------|-------------------------------------------------------|
| 90                                          | Clear Aperture (%):                                   |
| Commercial Polish                           | Back Surface:                                         |
| 4.00 +0.00/-0.10                            | Diameter (mm):                                        |
| 3.00 ±0.20                                  | Thickness (mm):                                       |
| Optical Properties                          |                                                       |
| 10-5                                        | Surface Quality:                                      |
| 99.8                                        | Reflection at DWL (%):                                |
| R <sub>abs</sub> >99.8% @ 266nm             | Coating Specification:                                |
| 263 - 268                                   | Wavelength Range (nm):                                |
| λ/10                                        | Surface Flatness (P-V):                               |
| Dielectric                                  | Coating Type:                                         |
| Laser Mirror (266nm)                        | Coating:                                              |
| 266                                         | Design Wavelength DWL (nm):                           |
| 0-45                                        | Angle of Incidence (°):                               |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: <input type="checkbox"/>                   |
| 2 J/cm <sup>2</sup> @ 266nm, 20ns, 20Hz     | Damage Threshold, Reference: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| <a href="#">View</a>  | Certificate of Conformance: |

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts