

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 4X, 40mm WVD, In-Line Compact TL™ Telecentric Lens



40mm WD, 4X, In-Line Version (Left) and VIS Version (Right)

Stock #67-322 3-4 DAYS



1



€1.065,00

ADD TO CART

Qty 1+

€1.065,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
50.26

Horizontal Field of View, 1/2" Sensor:
1.6mm

Horizontal Field of View, 2/3" Sensor:
2.2mm

Filter Thread:
M25.5 x 0.50 (Female) with Required Adapter [#88-212](#)
Sold Separately

Maximum Diameter (mm): 18.00
Weight (g): 45
Horizontal Field of View, 1/3" Sensor: 1.2mm
Numerical Aperture NA, Object Side: 0.099
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 6 (4)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.053
Typical Distortion @ 588nm (%): 0.1579
Front Thread: M16 x 0.5 (Female)
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 40
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/20
Coating: λ/4 MgF ₂
Compatible Light Guide/Source: 1/4" (0.312") and 1/8" (0.187")
Depth of Field (mm): ±0.05mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 2.2 x 1.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View