

[See all 24 Products in Family](#)

5mW, 520nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock #29-131 **1 In Stock**

− 1 + €243⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | €243,00 each |
| Qty 10+ | €219,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

36.00 **Length (mm):**

Optical Properties

| | |
|---|------------------------------------|
| TEM ₀₀ | Spatial Mode: |
| 520.00 ±10 | Wavelength (nm): |
| 3.5 Typical | Beam Diameter (mm): |
| <1 Typical | Beam Divergence (mrad): |
| Green | Color: |
| Electrical | |
| 5 | Output Power (mW): |
| 0 - 10 | Modulation Frequency (kHz): |
| Hardware & Interface Connectivity | |
| 7 | Operating Voltage (V): |
| Environmental & Durability Factors | |
| 23 to 27 | Operating Temperature (°C): |
| Regulatory Compliance | |
| View | Certificate of Conformance: |

Product Details

- TTL Modulation up to 10kHz
- Transverse Mode TEM₀₀
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation ([Sold Separately](#))

DPSS Pointing Lasers are diode pumped solid state lasers available in output powers ranging from 1 to 100mW. With their solid state design, these lasers offer excellent mode purity and low divergence, making them ideal for applications that require long projection distances. The turnkey design featuring integrated optics and electronics in a single package is suitable for a variety of plug and play operations. DPSS Pointing Lasers provide high brightness circular output beams and are ideal for many different OEM applications. TEC Controller or heatsink is required to maintain 23°C – 27°C operating temperature range.

Note: Power supplies, TEC Controller ([#19-476](#)), Line Projection Heads (for 532nm - [#37-093](#))(for 1064nm - [#37-097](#)), and mounting brackets ([#37-144](#)) are sold separately.