

[See all 125 Products in Family](#)

50.8mm Dia. 1550nm $\lambda/4$ Quartz Waveplate Zero Order



Stock #16-892 [CONTACT US](#)

− 1 + €1.790⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1+	€1.790,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Crystalline Waveplate **Type:**

Air Spaced **Configuration:**

Physical & Mechanical Properties

35.0 **Clear Aperture CA (mm):**

50.80 +0.00/-0.25 **Diameter (mm):**

6.00 +0.00/-0.25	Thickness (mm):
Crystalline	Construction:
<3	Parallelism (arcsec):
Optical Properties	
Laser V-Coat (1550nm)	Coating:
1550	Design Wavelength DWL (nm):
Crystal Quartz	Substrate: <input type="checkbox"/>
$\lambda/4$	Retardance:
20-10	Surface Quality:
< $\lambda/8$ @ 632.8 nm	Transmitted Wavefront, P-V:
$\pm\lambda/300$	Retardance Tolerance:
0.0001	Temperature Coefficient ($\lambda/^\circ\text{C}$):
$R_{\text{abs}} < 0.2\%$ @ on each surface	Coating Specification:
>10 J/cm ² @ 1064 nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>
0	Retardance Order:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$ and $\lambda/2$ Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than $\pm 1\%$ from the design wavelength of the waveplate. For applications with a greater than $\pm 1\%$ deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



Technical Information



