

50.8mm Dia., 3mm Thick, 7 - 14µm, ISP Optics Zinc Selenide IR Beamsplitter

See More by [ISP Optics](#)



Stock #25-031 3-4 DAYS

⊖ 1 ⊕ **€930,00**

ADD TO CART

Qty 1+

€930,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
85

Construction:
Plate

Diameter (mm):
50.80 +0.00/-0.13

Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 50/50 ±10% @ 7 - 14µm
Substrate: □ Zinc Selenide (ZnSe), CVD Grade
Surface Flatness (P-V): 2λ @ 633nm
Surface Quality: 60-40
Thickness (mm): 3.00 ±0.13
Type: Standard Beamsplitter
Wavelength Range (µm): 7 - 14
Wavelength Range (nm): 7000 - 14000
Model Number: BSP50-ZC-50-3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View