

50.8mm Dia. 632.8nm λ /4 Quartz Waveplate Zero Order



Stock **#85-049** CLEARANCE 3-4 DAYS

- 1 + **€1.086,95**

ADD TO CART

Qty 1+
€1.086,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
34.00

Coating:
Laser V-Coat (632.8nm)

Design Wavelength DWL (nm):
632.8

Diameter (mm):
50.80 +0.00/-0.25

Substrate: ☐
Crystal Quartz

Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 9.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View