

[See all 133 Products in Family](#)

TECHSPEC®

50.8mm Dia. x 190.6mm EFL, Protected Gold 50Å 90° Off-Axis Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock **#37-992** **4 In Stock**

☐ [Other Coating Options](#)

-

1

+

€420⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€420,00 each
Qty 6-10	€378,00 each
Qty 11-25	€360,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Off-Axis Parabolic Mirror	Type:
Physical & Mechanical Properties	
50.80 +0.0/-0.1	Diameter (mm):

Surface Roughness (□):	
<50 RMS	
Y Offset (mm):	
190.60	
Optical Properties	
Effective Focal Length EFL (mm):	
190.60	
Focal Length Tolerance (%):	
±1	
Radius of Curvature (mm):	
190.60	
Coating:	
Protected Gold (700-10000nm)	
Coating Type:	
Metal	
Coating Specification:	
R _{avg} ≥ 94% @ 700 - 800nm	
R _{avg} ≥ 97% @ 800 - 2,000nm	
R _{avg} ≥ 98% @ 2,000 - 12,000nm	
Off-Set Angle (°):	
90	
Parent Focal Length PFL (mm):	
95.3	
Surface Figure, RMS:	
λ/8	
Wavelength Range (nm):	
700 - 10000	
Surface Quality:	
80-50	
Substrate:	
Aluminum 6061-T6	
Reflected Wavefront, RMS:	
λ/4	

Threading & Mounting	
Compatible Mounting Plates:	
#47-112	


Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 209:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- Bare or Protected Gold Coating for NIR and IR Applications
- 50Å and 100Å Surface Roughness Options
- 15°, 30°, 45°, 60°, or 90° Offset Angles
- Aluminum and Silver Coated Mirrors Also Available

TECHSPEC® Gold Off-Axis Parabolic Mirrors (OAPs) are designed for minimal scatter loss in light focusing applications. Available with bare or protected gold coatings, these OAP mirrors offer excellent reflectivity from the near infrared (NIR) to the far infrared (IR). Multiple surface roughness options are available in offset angles from 15 to 90°, providing flexibility for system designs. TECHSPEC® Gold Off-Axis Parabolic Mirrors are commonly used in IR systems such as FLIR and FTIR, as well as IR lasers including quantum cascade lasers (QCLs). Mounting plates with holes perpendicular to the optical axis for post mounting are also available.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
