

[See all 195 Products in Family](#)

**TECHSPEC® 50.8mm Dia. x 250mm FL, Uncoated, Laser Grade PCX Lens**



TECHSPEC Laser Grade PCXLenses

Stock **#70-006** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €407<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€407,00 each
Qty 6-25	€326,00 each
Qty 26-49	€313,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

50.80 +0.00/-0.025 **Diameter (mm):**

<1	Centering (arcmin):
8.00	Center Thickness CT (mm):
5.15	Edge Thickness ET (mm):
45.72	Clear Aperture CA (mm):
Protective as needed	Bevel:
<b>Optical Properties</b>	
250.00 @ 355nm	Effective Focal Length EFL (mm):
244.514	Back Focal Length BFL (mm):
Uncoated	Coating:
<a href="#">Fused Silica</a> (Corning 7980)	Substrate: <input type="checkbox"/>
10-5	Surface Quality:
$\lambda$	Power (P-V) @ 632.8nm:
M10 $\pm$ 1	Irregularity (P-V) @ 632.8nm:
114.62	Radius R <sub>1</sub> (mm):
4.92	f#:
0.10	Numerical Aperture NA:
200 - 2200	Wavelength Range (nm):

<b>Regulatory Compliance</b>	
<a href="#">View</a>	Certificate of Conformance:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:


- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- M10 Surface Accuracy

TECHSPEC® Laser Grade PCX Lenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring M10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCX Lenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.



## Technical Information

**532nm V-Coat**  
 $R_{(obs)} < 0.25\% @ 532nm$



**355nm V-Coat**  
 $R_{(obs)} < 0.25\% @ 355nm$



**1064nm V-Coat**  
 $R_{(obs)} < 0.25\% @ 1064nm$

