

[See all 195 Products in Family](#)

TECHSPEC® 50.8mm Dia. x 250mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#70-006** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €407⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€407,00 each
Qty 6-25	€326,00 each
Qty 26-49	€313,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

50.80 +0.00/-0.025 **Diameter (mm):**

<1	Centering (arcmin):
8.00	Center Thickness CT (mm):
5.15	Edge Thickness ET (mm):
45.72	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

250.00 @ 355nm	Effective Focal Length EFL (mm):
244.514	Back Focal Length BFL (mm):
Uncoated	Coating:
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
10-5	Surface Quality:
λ	Power (P-V) @ 632.8nm:
M10 \pm 1	Irregularity (P-V) @ 632.8nm:
114.62	Radius R ₁ (mm):
4.92	f#:
0.10	Numerical Aperture NA:
200 - 2200	Wavelength Range (nm):


Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------


Product Details

- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- M10 Surface Accuracy



TECHSPEC® Laser Grade PCXLenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring M10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.




Technical Information



355nm V-Coat
 $R_{(obs)} < 0.25\% @ 355nm$



1064nm V-Coat
 $R_{(obs)} < 0.25\% @ 1064nm$



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).