


TECHSPEC[®] 50mm Dia., 3mm Thick, Uncoated, $\lambda/4$ Fused Silica Window



TECHSPEC[®] $\lambda/4$ UV Fused Silica Windows

Stock **#70-532** 20+ In Stock

-

1

+

€202⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€202,00 each
Qty 6-25	€161,00 each
Qty 26-49	€151,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

45.00

Clear Aperture CA (mm):

Diameter (mm):

50.00 +0.00/-0.10	
3.00 ±0.10	Thickness (mm):
<1	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
522.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
Fused Silica	Substrate: ☐
1.458	Index of Refraction (n _d):
40-20	Surface Quality:
λ/4	Transmitted Wavefront, P-V:
67.8	Abbe Number (v _d):
200 - 2200	Wavelength Range (nm):

Material Properties

2.20	Density (g/cm³):
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume




Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details






- Available Uncoated or BBAR Coated for UV, Visible, and NIR
- Ideal for Imaging Applications
- Circular and Rectangular Sizes from 5 to 200mm
- [1λ](#) or [λ/10](#) UV Fused Silica Windows Also Available

TECHSPEC® λ/4 UV Fused Silica Windows are manufactured with 40-20 surface quality and λ/4 transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC λ/4 UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

Technical Information



FUSED SILICA																																			
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																																		
200	92																																		
400	94																																		
600	94																																		
800	94																																		
1000	94																																		
1200	94																																		
1400	92																																		
1600	94																																		
1800	94																																		
2000	94																																		
2200	90																																		
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>96</td></tr><tr><td>600</td><td>96</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>95</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	94	400	96	600	96	800	95	1000	95	1200	95	1400	93	1600	95	1800	95	2000	95	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																																		
200	94																																		
400	96																																		
600	96																																		
800	95																																		
1000	95																																		
1200	95																																		
1400	93																																		
1600	95																																		
1800	95																																		
2000	95																																		
2200	90																																		
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>250</td><td>98</td></tr><tr><td>300</td><td>99</td></tr><tr><td>350</td><td>99</td></tr><tr><td>400</td><td>99</td></tr><tr><td>425</td><td>100</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>78</td></tr><tr><td>1400</td><td>75</td></tr><tr><td>1600</td><td>75</td></tr><tr><td>1800</td><td>75</td></tr><tr><td>2000</td><td>76</td></tr><tr><td>2200</td><td>77</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	250	98	300	99	350	99	400	99	425	100	500	99	600	98	800	95	1000	85	1200	78	1400	75	1600	75	1800	75	2000	76	2200	77	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																																		
200	75																																		
250	98																																		
300	99																																		
350	99																																		
400	99																																		
425	100																																		
500	99																																		
600	98																																		
800	95																																		
1000	85																																		
1200	78																																		
1400	75																																		
1600	75																																		
1800	75																																		
2000	76																																		
2200	77																																		

	
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$ $R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Wavelength (nm) Fused Silica with YAG-BBAR Coating Typical Transmission The graph shows the typical transmission of a 3mm thick fused silica window with a YAG-BBAR coating. The y-axis represents Transmittance (T) in percent, ranging from 70 to 100. The x-axis represents Wavelength in nanometers (nm), ranging from 200 to 1600. The transmission curve is red, showing high transmittance across most of the visible and near-infrared spectrum. A blue shaded region highlights the coating design wavelength range from 500 nm to 1100 nm, where the transmittance is consistently above 95%.	Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{\text{abs}} \leq 0.25\%$ @ 532nm $R_{\text{abs}} \leq 0.25\%$ @ 1064nm $R_{\text{avg}} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
--	--