

TECHSPEC® 50mm Dia., 3mm Thick, UV-AR Coated, λ /4 Fused Silica Window



TECHSPEC® λ /4 UV Fused Silica Windows

Stock **#72-414** 4 In Stock

-

1

+

€238⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€238,00 each
Qty 6-25	€190,00 each
Qty 26-49	€178,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

45.00

Clear Aperture CA (mm):

Diameter (mm):

50.00 +0.00/-0.10	
3.00 ±0.10	Thickness (mm):
<1	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
522.00	Knoop Hardness (kg/mm²):

Optical Properties

UV-AR (250-425nm)	Coating:
Fused Silica (Corning 7980)	Substrate: ☐
1.458	Index of Refraction (n _d):
40-20	Surface Quality:
λ/4	Transmitted Wavefront, P-V:
67.8	Abbe Number (v _d):
R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm	Coating Specification:
250 - 450	Wavelength Range (nm):
3 J/cm² @ 355nm, 10ns	Damage Threshold, Reference:

Material Properties

2.20	Density (g/cm³):
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:




Product Details

- Available Uncoated or BBAR Coated for UV, Visible, and NIR
 - Ideal for Imaging Applications
 - Circular and Rectangular Sizes from 5 to 200mm
 - 1λ or λ/10 UV Fused Silica Windows Also Available
- TECHSPEC® λ/4 UV Fused Silica Windows are manufactured with 40-20 surface quality and λ/4 transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC λ/4 UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

Technical Information



FUSED SILICA																											
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																										
200	92																										
400	94																										
600	94																										
800	94																										
1000	94																										
1200	94																										
1400	92																										
1600	94																										
1800	94																										
2000	94																										
2200	90																										
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>96</td></tr><tr><td>600</td><td>96</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>95</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	94	400	96	600	96	800	95	1000	95	1200	95	1400	93	1600	95	1800	95	2000	95	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																										
200	94																										
400	96																										
600	96																										
800	95																										
1000	95																										
1200	95																										
1400	93																										
1600	95																										
1800	95																										
2000	95																										
2200	90																										
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>250</td><td>98</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>85</td></tr><tr><td>1400</td><td>78</td></tr><tr><td>1600</td><td>75</td></tr><tr><td>1800</td><td>75</td></tr><tr><td>2000</td><td>75</td></tr><tr><td>2200</td><td>76</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	250	98	400	98	600	98	800	98	1000	95	1200	85	1400	78	1600	75	1800	75	2000	75	2200	76	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																										
200	75																										
250	98																										
400	98																										
600	98																										
800	98																										
1000	95																										
1200	85																										
1400	78																										
1600	75																										
1800	75																										
2000	75																										
2200	76																										

	
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$ $R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

