

[See all 81 Products in Family](#)

TECHSPEC® 50mm Dia. 320 - 450nm Broadband $\lambda/10$ Mirror



Stock **#37-571** **4 In Stock**

- 1 + €284⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€284,00 each
Qty 6-25	€227,00 each
Qty 26-49	€213,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

Diameter (mm):

50.00 +0.00/-0.20

10.00 ±0.20

Thickness (mm):

Fine Grind

Back Surface:

90

Clear Aperture (%):

Ground, 0.5mm max bevel

Edges:

<3

Parallelism (arcmin):

Optical Properties

Dielectric

Coating Type:

Dielectric Mirror (320-450nm)

Coating:

λ/10

Surface Flatness (P-V):

320 - 450

Wavelength Range (nm):

Fused Silica (Corning 7980)

Substrate:

0-45

Angle of Incidence (°):

Coating Specification:
R_{avg} >98% @ 340 - 488nm (0°, All Polarizations)
R_{avg} >98% @ 320 - 450nm (45°, All Polarizations)
R_{avg} >99% @ 320 - 450nm (45°, S-Polarization)

20-10

Surface Quality:

0.5 J/cm² @ 355nm, 20ns, 20Hz

Damage Threshold, By Design:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 253:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric λ/10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric λ/10 Mirrors are designed for applications from the UV to the near-infrared spectra.

Technical Information



Compatible Mounts
