

TECHSPEC® 50mm Dia x 25mm FL 8-12µm Coated, Ge Aspheric Lens



Stock **#87-997** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€1.888,00**

ADD TO CART

Qty 1-5
€1.888,00
Qty 6+
€1.510,40
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 4000nm

Numerical Aperture NA:
1.00

Back Focal Length BFL (mm): 20.64
Substrate: ☐ Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <3.0% @ 8 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 45
Edge Thickness ET (mm): 2.5
Center Thickness CT (mm): 7.75 ±0.10
f/#: 0.5
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 49.34
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant