

TECHSPEC® 50mm Dia. x 350mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-289-INK** [CONTACT US](#)
[Other Coating Options](#)

- 1 + **€190,00**

ADD TO CART

Qty 1-5
€190,00
Qty 6+
€152,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):

350.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 344.32
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 49.00
Centering (arcmin): <1
Center Thickness CT (mm): 12.00 ±0.20
Center Thickness CT 1 (mm): 8.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R ₁ (mm): 227.16
Radius R ₂ (mm): -174.83
Radius R ₃ (mm): -571.49
Edge Thickness ET (mm): 10.07
Substrate: ☐ N-BAK4 / N-SF10
Surface Quality: 40-20
f/#: 7.00
Numerical Aperture NA: 0.07
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View