


[All Products](#) / [Optics](#) / [Optical Lenses](#)

[See all 9 Products in Family](#)

# 5.0" x 5.0", FL 2.60



Infrared (IR) Fresnel Lenses

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€42<sup>,00</sup>

ADD TO CART

Volume Pricing	
Qty 1-10	€42,00 each
Qty 11-49	€38,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

[EO Spec Sheet](#)

## General

Type: Fresnel Lens

## Physical & Mechanical Properties

Center Thickness CT (inches): 0.02

Dimensions (inches): 5.0 x 5.0

Dimensions (mm): 127.0 x 127.0

Effective Diameter (inches): 4.0

Young's Modulus (GPa): 0.40 - 1.24

## Optical Properties

Effective Focal Length EFL (mm): 66.04

Substrate: Poly IR

Coating: Uncoated

Wavelength Range (nm): 8000 - 14000

Effective Focal Length EFL (inches): 2.60

Groove Density (grooves/inch): 100.00

Index of Refraction (n<sub>d</sub>): Visible (Sodium D Line): 1.52  
8-14µm: 1.53  
15µm+: 1.48

Wavelength Range (µm): 8 - 14

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C): 11 - 13

Flexural Modulus (psi): (100-260) x 10<sup>3</sup>

Shore Hardness: D60-70

## Environmental & Durability Factors

**Operating Temperature (°C):** 100.00

## Regulatory Compliance

**RoHS 2015:** **Compliant**

**Reach 242:** **Compliant**

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

## Product Details

- Excellent Collecting Optics for Infrared Detectors
- Minimal Absorption Loss in the 8-14 $\mu$ m Region

IR Fresnel lenses are molded in a flexible, 0.015" (0.457mm) thick, milky white plastic. Advantages of this product are: least absorption loss in the 8-14 $\mu$ m region, extremely thin with consistent thickness across the lens, large apertures and minimal thermal expansion. The design of an infrared-transmitting Fresnel lens involves many complex considerations. The grooved side of a Fresnel lens should face the longer conjugate (away from the detector when used to collect radiation). If the smooth side needs to face the longer conjugate for some nonoptical reason, the maximum aperture of the lens should be f/1.0. In this case, total internal reflection keeps all radiation from the area of the lens past f/1.0 from reaching the image. Even when the grooves face the longer conjugate, the portion of the lens past f/1.0 contributes a diminished amount and there is no significant contribution past f/0.5.

## Technical Information

Effect of Sunlight	None to Slight
Effect of Ultraviolet	UV Stabilized
Effect of Weak Acids	Very Little
Effect of Strong Acids	Attacked by Oxidizing Acids
Effect of Weak Alkalies	Very Little
Effect of Strong Alkalies	Very Little
Effect of Organic Solvents	Little below 60°C (140°F)

## Frequently Purchased Together



#32-796 - 2.0" x 2.0", FL 0.79", IR Fresnel Lens  
**€39,50**

Qty



#32-798 - 2.3" x 2.3", FL 1.2", IR Fresnel Lens  
**€39,50**

Qty



#32-590 - 3.0" x 3.0", 2.6" Focal Length, Fresnel Lens  
**€50,50**

Qty



#32-797 - 1.5" x 1.5", FL 0.92", IR Fresnel Lens  
**€39,50**

Qty



## Resources

**Media Type**

- Video
- Glossary
- Scientific Paper
- Application Note
- FAQ

▶ VIDEO

Etched Lens

GLOSSARY

Etched Lens

📄 SCIENTIFIC PAPER

Advantages of using engineered chalcogenide...

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

▶ VIDEO

Infrared Light

GLOSSARY

Short Wave Infrared (SWIR)

📄 APPLICATION NOTE

Advantages of Using Meniscus Lenses in...

[View More](#)