

50mm Travel, Motorized Linear Actuator, Integrated Controller, Manual Control

See More by [Zaber™](#)



Stock #22-628 **2 In Stock**

⊖ 1 ⊕ €1.370⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€1.370,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**

Yes **Manual Control/ LED Indicators:**

Zaber Technologies Inc. **Manufacturer:**

Stepper (2 Phase) **Type of Motor:**

Physical & Mechanical Properties

Linear (X)

Type of Movement:

50.8

Travel (mm):

55 (Unidirectional)

Accuracy (μm):

<15

Backlash (μm):

162.5 L x 49.4 W x 20.0 H

Dimensions (mm):

<1

Repeatability (μm):

0.000029 to 30

Speed (mm/s):

25

Thrust (N):

0.16

Weight (kg):

Optical Properties

0.047625

Resolution (μm):

Electrical

180

Maximum Operating Current (mA):

Hardware & Interface Connectivity

Precision Lead Screw

Type of Drive:

24-48 VDC

Power Supply:

RS-232

Computer Interface:

Threading & Mounting

3/8-32 Nut, 3/8" Shank or M3 Screws

Mount:

Environmental & Durability Factors

0 to 50

Operating Temperature ($^{\circ}\text{C}$):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 247:

Product Details

- Miniature, Robust Design
- Integrated Motor and Controller
- Controlled Manually or via RS-232 Serial Interface
- Available with Integrated, 250 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ High Accuracy Linear Actuators feature 50nm resolution with up to 50mm travel distance. These computer-controlled, self-contained linear actuators include a stepper motor and a built-in controller that can connect directly a computer's RS-232 port while requiring only the included 15V power supply. Encoder versions are available for all travel lengths and include 250 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ High Accuracy Linear Actuators also feature an industry standard 3/8" shank that fits most common stages. The actuator shaft does not rotate and will not transmit any torque to the translation stage. When used manually, the actuator can be monitored using a computer if needed.

Note: A 6ft. data cable, RS-232 adapter, and universal power supply are sold separately as accessories