


TECHSPEC[®] 5mm Dia. Protected Gold, λ /4 Mirror



Stock **#48-410** [CONTACT US](#)

-

1

+

€83^{.50}

ADD TO CART

Volume Pricing	
Qty 1-5	€83,50 each
Qty 6-25	€66,50 each
Qty 26-49	€63,00 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat MirrorType:

Physical & Mechanical Properties

5.00Diameter (mm):

2.00 ±0.25Thickness (mm):

	Back Surface:
Commercial Polish	
	Bevel:
Protective as needed	
	Clear Aperture (%):
83	
	Dimensional Tolerance (mm):
±0.25	

	Edges:
Fine Ground	

Optical Properties

	Wavelength Range (µm):
0.7 - 10	

	Coating Type:
Metal	

	Coating:
Protected Gold (700-10000nm)	

	Surface Flatness (P-V):
λ/4	

	Wavelength Range (nm):
700 - 10000	

	Substrate: 
--	--

	Coating Specification:
R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	

	Surface Quality:
60-40	

	Damage Threshold, Reference: 
0.8 J/cm ² @ 1064nm, 10ns	

Regulatory Compliance

	RoHS 2015:
Compliant	

	Certificate of Conformance:
View	

	Reach 247:
Compliant	

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

TECHSPEC® λ/4 First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The coated surface should be oriented to reflect incident light. TECHSPEC λ/4 First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration. The mirrors have available coatings of enhanced aluminum, protected aluminum, protected silver, and protected gold.

Note: Surface flatness is measured before coating.

A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

Compatible Mounts